

## Electrostatic Discharged Protection Devices (ESD) Data Sheet

### Description

Brightking's UFS08A2.8L04-R2.0 component is designed to protect low voltage state-of-the-art CMOS semiconductors from transients caused by electrostatic discharge (ESD), cable discharge events (CDE), lightning and other induced voltage surges. The device provides low stand-off voltages with significant reductions in leakage currents and capacitance over silicon avalanche diode processes.

The UFS08A2.8L04-R2.0 features integrated low capacitance compensation diodes that reduce the max capacitance 2pF per line.

This combined with low leakage current, means signal integrity preserved in high-speed applications such as 10/100/1000 Ethernet.




Contact : ±30kV  
Air : ±30kV



### Features

- IEC61000-4-2 ESD 30KV Air, 30KV contact compliance
- SOIC-08 surface mount package
- Protects four I/O lines
- Peak power dissipation of 600W under 8/20μs waveform
- Working voltage: 2.8V
- Low leakage current
- Low operating and clamping voltages
- Solid-state silicon avalanche technology
- Lead Free/RoHS compliant
- Solder reflow temperature: Pure Tin-Sn, 260~270°C
- Flammability rating UL 94V-0
- Meets MSL level 1, per J-STD-020
- Marking: B SLVU2.8-4



### Applications

- |   |   |
|---|---|
| <ul style="list-style-type: none"> <li>● 10/100/1000 Ethernet</li> <li>● WAN/LAN Equipment</li> <li>● High current switching systems</li> <li>● Desktops, Servers and Notebook</li> </ul> | <ul style="list-style-type: none"> <li>● Instrumentation</li> <li>● Analog inputs</li> <li>● Base stations</li> </ul> |
|---|---|

### Maximum Ratings


Rating	Symbol	Value	Unit
Peak pulse power (tp=8/20μs waveform)	P <sub>PP</sub>	600	W
ESD voltage (Contact discharge)	V <sub>ESD</sub>	±30	kV
ESD voltage (Air discharge)		±30	
Storage & operating temperature range	T <sub>STG</sub> , T <sub>J</sub>	-55~+150	°C

Electrical Characteristics ( $T_J=25^\circ\text{C}$ )

Parameter	Symbol	Condition	Min.	Max.	Unit
Reverse stand-off voltage	$V_{RWM}$			2.8	V
Reverse breakdown voltage	$V_{BR}$	$I_{BR}=1\text{mA}$	3		V
Reverse leakage current	$I_R$	$V_R=2.8\text{V}$ Each I/O pin		1	$\mu\text{A}$
Clamping voltage ( $tp=8/20\mu\text{s}$ )	$V_C$	$I_{PP}=5\text{A}$		10	V
Peak pulse current ( $tp=8/20\mu\text{s}$ )	$I_{PP}$			24	A
Off state junction capacitance	$C_J$	0Vdc,f=1MHz Between I/O pins and GND		2	pF
		0Vdc,f=1MHz Line to Line, two I/O pins connected together on each line (Note)		4	pF

Note: Ratings with two pins connected together per the recommended configuration (ie pin 1 connected to pin 8, pin 2 connected to pin 7, pin 3 connected to pin 6, pin 4 connected to pin 5).

## Applications Information



## Typical Characteristics Curves

Figure 1. Power Derating Curve




Figure 2. Pulse Waveforms




Figure 3. Capacitance vs. Reverse Voltage






Figure 4. Clamping Voltage vs. Peak Pulse Current



## Recommended Soldering Conditions


### Reflow Soldering



### Recommended Conditions

Profile Feature	Pb-Free Assembly
Average ramp-up rate (T <sub>L</sub> to T <sub>P</sub> )	3°C/second max.
Preheat	
-Temperature Min (T <sub>S min</sub> )	150°C
-Temperature Max (T <sub>S max</sub> )	200°C
-Time (min to max) (t <sub>s</sub> )	60-180 seconds
T <sub>S max</sub> to T <sub>L</sub>	
-Ramp-up Rate	3°C/second max.
Time maintained above:	
-Temperature (T <sub>L</sub> )	217°C
-Time (t <sub>L</sub> )	60-150 seconds
Peak Temperature (T <sub>P</sub> )	260°C
Time within 5°C of actual Peak Temperature (t <sub>P</sub> )	20-40 seconds
Ramp-down Rate	6°C/second max.
Time 25°C to Peak Temperature	8 minutes max.



## Dimensions (SOIC-08)



Symbol	Dimension			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	4.80	5.00	0.189	0.197
B	5.80	6.20	0.228	0.244
C	3.80	4.00	0.150	0.157
D	1.27		0.050	
E	0.33	0.51	0.013	0.020
F	0.40	1.27	0.016	0.050
G	0.19	0.25	0.007	0.010
H	1.35	1.75	0.053	0.069
H1	0.10	0.25	0.004	0.010
H2	1.45		0.057	

Recommended Soldering Pad Layout

## Packaging

Tape	Symbol	Dimension (mm)
	W	12.00±0.30
	P0	4.00±0.10
	P1	8.00±0.10
	P2	2.00±0.10
	D0	Φ1.55±0.10
	D1	Φ1.55±0.05
	E	1.75±0.10
	F	5.50±0.10
	A	6.50±0.10
	B	5.40±0.10
	K	2.00±0.10
	t	0.30±0.05
Reel	D	Φ330.0±3.0
	D2	Φ13.0
	W1	13.5
	Quantity: 2500PCS	