

Electrostatic Discharged Protection Devices (ESD) Data Sheet

Description

Brightking's LES16CXXL08 Series have been specifically designed to protect sensitive components which are connected to data and transmission lines from overvoltage caused by electrostatic discharge (ESD), electrical fast transients (EFT), and lightning.

The low capacitance array configuration allows the user to protect eight high-speed data or I/O lines. The high surge capability makes the series suitable for telecommunication systems operating in harsh transient environments.

The low inductance construction minimizes voltage overshoot during high current surges.




Contact: ±30kV
Air : ±30kV




Features

- IEC61000-4-2 ESD 30KV Air, 30KV contact compliance
- SOIC-16 surface mount package
- Protects eight I/O lines
- Peak power dissipation of 500W under 8/20μs waveform
- Working voltage: 5V,24V
- Low leakage current
- Low capacitance and clamping voltage
- Solid-state silicon avalanche technology
- Lead Free/RoHS compliant
- Solder reflow temperature: Pure Tin-Sn, 260~270°C
- Flammability rating UL 94V-0
- Meets MSL level 1, per J-STD-020



Applications

- Wireless communication circuit
- WAN equipment
- CSU/DSU
- Multiplexers
- Routers
- ISP equipment
- RS-232 (V.28)
- RS-422 (V.11, X.21)
- Ethernet-10/100 base T
- Low-voltage ASICs



Maximum Ratings

| Rating | Symbol | Value | Unit |
|---------------------------------------|-----------------------------------|----------|------|
| Peak pulse power (tp=8/20μs waveform) | P _{PP} | 500 | W |
| ESD voltage (Contact discharge) | V _{ESD} | ±30 | kV |
| ESD voltage (Air discharge) | | ±30 | |
| Storage & operating temperature range | T _{STG} , T _J | -55~+150 | °C |

Electrical Characteristics (T_J=25°C)

LES16C05L08(MARKING:B 16LCC05-8)

| Parameter | Symbol | Condition | Min. | Max. | Unit |
|--------------------------------|------------------|---|------|------|------|
| Reverse stand-off voltage | V _{RWM} | | | 5 | V |
| Reverse breakdown voltage | V _{BR} | I _{BR} =1mA | 6 | | V |
| Reverse leakage current | I _R | V _R =5V Each I/O pin | | 1.0 | μA |
| Clamping voltage (tp=8/20μs) | V _C | I _{PP} =1A | | 9.8 | V |
| Clamping voltage (tp=8/20μs) | V _C | I _{PP} =10A | | 17 | V |
| Peak pulse current (tp=8/20μs) | I _{PP} | | | 20 | A |
| Off state junction capacitance | C _J | 0Vdc,f=1MHz Between I/O pins and GND | | 15 | pF |

LES16C24L08(MARKING:B LC24C-8)

| Parameter | Symbol | Condition | Min. | Max. | Unit |
|--------------------------------|------------------|---|------|------|------|
| Reverse stand-off voltage | V _{RWM} | | | 24 | V |
| Reverse breakdown voltage | V _{BR} | I _{BR} =1mA | 26.7 | | V |
| Reverse leakage current | I _R | V _R =24V Each I/O pin | | 1 | μA |
| Clamping voltage (tp=8/20μs) | V _C | I _{PP} =1A | | 40 | V |
| Clamping voltage (tp=8/20μs) | V _C | I _{PP} =10A | | 57 | V |
| Peak pulse current (tp=8/20μs) | I _{PP} | | | 10 | A |
| Off state junction capacitance | C _J | 0Vdc,f=1MHz Between I/O pins and GND | | 15 | pF |

Typical Characteristics Curves

Figure 1. Power Derating Curve




Figure 2. Pulse Waveforms




Figure 3. Non-Repetitive Peak Pulse vs. Pulse Time







Figure 4. Capacitance vs. Reverse Voltage



Recommended Soldering Conditions





Dimensions (SOIC-16)



| Symbol | Dimension | | | |
|--------|-------------|------|--------|-------|
| | Millimeters | | Inches | |
| | Min. | Max. | Min. | Max. |
| A | 9.80 | 10.0 | 0.386 | 0.394 |
| B | 5.80 | 6.20 | 0.228 | 0.244 |
| C | 3.80 | 4.00 | 0.150 | 0.157 |
| D | 1.27 | | 0.05 | |
| E | 0.35 | 0.51 | 0.014 | 0.020 |
| F | 0.50 | 0.90 | 0.020 | 0.035 |
| G | 0.19 | 0.25 | 0.007 | 0.010 |
| H | 1.35 | 1.75 | 0.053 | 0.069 |
| H1 | 0.10 | 0.25 | 0.004 | 0.010 |

Recommended Soldering Pad Layout

Packaging

| Tape | Symbol | Dimension (mm) |
|---|-------------------|----------------|
|  | W | 16.00±0.30 |
| | P0 | 4.00±0.10 |
| | P1 | 8.00±0.10 |
| | P2 | 2.00±0.10 |
| | D0 | Φ1.55±0.10 |
| | D1 | Φ1.55±0.10 |
| | E | 1.75±0.10 |
| | F | 7.50±0.10 |
| | A | 6.55±0.20 |
| | B | 10.40±0.20 |
| | K | 2.00±0.20 |
| | t | 0.30±0.05 |
| 13" Reel | D | Φ330.0±3.0 |
|  | D2 | Φ13.0 |
| | W1 | 17.5 |
| | Quantity: 2500PCS | |