


Thermistor-type Devices Certified for Canada - Component


COMPANY

BESTBRIGHT ELECTRONICS CO LTD

#3 Bldg, Modern enterprise accelerator park,
Song Shan Lake High-tech Industrial development zone
Dongguan, Guangdong 523808 China

E482628

Marking: Company name or tradename "E482628", "YAGEO", or trademark , model designation, and the

Recognized Component Mark for Canada 

Note: For additional marking information, refer to the [Guide Information Page](#).

View model for additional information

Inrush-limiting NTC, Model(s): 08SP003, N08SP003, BKN08SP003@#*****, 08SP004, N08SP004, BKN08SP004@#*****, 08SP005, BKN08SP005, N08SP005, 08SP006, BKN08SP006, N08SP006, 08SP008, BKN08SP008, N08SP008, 08SP010, BKN08SP010, N08SP010, 08SP012, N08SP012, BKN08SP012@#*****, 08SP015, BKN08SP015, N08SP015, 08SP020, N08SP020, BKN08SP020@#*****, 08SP022, N08SP022, BKN08SP022@#*****, 08SP033, N08SP033, BKN08SP033@#*****, N10SP001, BKN10SP001@#*****, N10SP002, BKN10SP002@#*****, N10SP003, BKN10SP003, N10SP004, BKN10SP004, N10SP005, BKN10SP005, N10SP006, BKN10SP006, N10SP007, BKN10SP007, N10SP008, BKN10SP008, N10SP010, BKN10SP010, N10SP012, BKN10SP012, N10SP015, BKN10SP015@#*****, N10SP016, BKN10SP016, N10SP020, BKN10SP020, N10SP025, BKN10SP025, N10SP033, BKN10SP033@#*****, N10SP047, BKN10SP047@#*****, N10SP050, BKN10SP050, N10SP080, BKN10SP080, N10SP0R7, BKN10SP0R7@#*****, N10SP120, BKN10SP120, N10SP150, BKN10SP150@#*****, N10SP1R3, BKN10SP1R3@#*****, N10SP1R5, BKN10SP1R5@#*****, N10SP2R5, BKN10SP2R5, N13SP003, BKN13SP003@#*****, N13SP004, BKN13SP004@#*****, N13SP005, BKN13SP005, N13SP006, BKN13SP006@#*****, N13SP007, BKN13SP007@#*****, N13SP008, BKN13SP008, N13SP010, BKN13SP010, N13SP012, BKN13SP012@#*****, N13SP016, BKN13SP016, N13SP018, BKN13SP018@#*****, N13SP020, BKN13SP020@#*****, N13SP025, BKN13SP025@#*****, N13SP060, BKN13SP060@#*****, N13SP0R7, BKN13SP0R7@#*****, N13SP1R3, BKN13SP1R3@#*****, N13SP1R5, BKN13SP1R5@#*****, N13SP2R5, BKN13SP2R5@#*****, N15SP003, BKN15SP003, N15SP004, BKN15SP004, N15SP005, BKN15SP005, N15SP006, BKN15SP006, N15SP007, BKN15SP007, N15SP008, BKN15SP008, N15SP010, BKN15SP010, N15SP012, BKN15SP012, N15SP015, BKN15SP015, N15SP016, BKN15SP016, N15SP020, BKN15SP020, N15SP022, BKN15SP022@#*****, N15SP025, BKN15SP025, N15SP030, BKN15SP030@#*****, N15SP033, BKN15SP033@#*****, N15SP040, BKN15SP040, N15SP047, BKN15SP047, N15SP055, BKN15SP055@#*****, N15SP080, BKN15SP080, N15SP0R7, BKN15SP0R7@#*****, N15SP120, BKN15SP120, N15SP1R3, BKN15SP1R3, N15SP1R5, BKN15SP1R5, N15SP2R5, BKN15SP2R5, N20SP001, BKN20SP001@#*****, N20SP002, BKN20SP002@#*****, N20SP004, BKN20SP004@#*****, N20SP005, BKN20SP005, N20SP006, BKN20SP006, N20SP007, BKN20SP007@#*****, N20SP008, BKN20SP008@#*****, N20SP010, BKN20SP010, N20SP012, BKN20SP012, N20SP016, BKN20SP016@#*****, N20SP020, BKN20SP020@#*****, N20SP025, BKN20SP025@#*****, N20SP0R7, BKN20SP0R7, N20SP120, BKN20SP120, N20SP1R3, BKN20SP1R3, N20SP2R5, BKN20SP2R5@#*****, N25SP001, BKN25SP001@#*****, N25SP002, BKN25SP002@#*****, N25SP003, BKN25SP003@#*****, N25SP004, BKN25SP004@#*****, N25SP005, BKN25SP005@#*****, N25SP007, BKN25SP007@#*****, N25SP008, BKN25SP008@#*****, N25SP010, BKN25SP010@#*****, N25SP012, BKN25SP012@#*****, N25SP015, BKN25SP015@#*****, N25SP018, BKN25SP018@#*****, N25SP020, BKN25SP020@#*****, N25SP0R7, BKN25SP0R7@#*****, N25SP1R5, BKN25SP1R5@#*****, N25SP2R5, BKN25SP2R5@#*****, N25SP4R7, BKN25SP4R7@#*****, N25SP6R8, BKN25SP6R8@#*****, NTB01-010, BKNTB01#010@#*****, NTB01-012, BKNTB01#012@#*****, NTBR3-020, BKNTBR3#020@#*****, NTBR3-025, BKNTBR3#025@#*****, NTD03, BKNTD03, NTD04, BKNTD04, NTE03, BKNTTE03, NTE03-050, BKNTTE03#050@#*****, NTE04, BKNTTE04, NTE05, BKNTTE05, NTE08-0R7, BKNTTE08#0R7@#*****, NTG04, BKNTG04, NTG05, BKNTG05, NTG06-003, BKNTG06#003@#*****, NTG06-004, BKNTG06#004@#*****, NTG06-005, BKNTG06#005@#*****, NTG06-006, BKNTG06#006@#*****, NTG06-007, BKNTG06#007@#*****, NTG07, BKNTG07, NTG09-0R7, BKNTG09#0R7@#*****, NTJ04-025, BKNTJ04#025@#*****, NTJ04-030, BKNTJ04#030@#*****, NTJ04-033, BKNTJ04#033@#*****, NTJ04-040, BKNTJ04#040@#*****, NTJ04-047, BKNTJ04#047@#*****, NTJ04-050, BKNTJ04#050@#*****, NTJ04-055, BKNTJ04#055@#*****, NTJ05-013, BKNTJ05#013@#*****, NTJ05-014,

,BKNTJ05#014@#*****, NTJ05-015,,BKNTJ05#015@#*****, NTJ05-018,,BKNTJ05#018@#*****, NTJ05-020,,BKNTJ05#020@#*****,
NTJ05-022,,BKNTJ05#022@#*****, NTJ06,,BKNTJ06,,NTJ08,,BKNTJ08,,NTJ09,,BKNTJ09,,NTJ11-0R7,,BKNTJ11#0R7@#*****, NTL08,
BKNTL08,,NTL10,,BKNTL10,,NTL12,,BKNTL12

Inrush-limiting NTC, Model(s): NTB01-015,,05SP015,,N05SP015,,BKNTB01#015@#*****,BKN05SP015@#*****

Inrush-limiting NTC, Model(s): NTB01-016,,05SP016,,N05SP016,,BKNTB01#016@#*****,BKN05SP016@#*****

Inrush-limiting NTC, Model(s): NTB01-020,,05SP020,,N05SP020,,BKNTB01#020@#*****,BKN05SP020@#*****

Inrush-limiting NTC, Model(s): NTB01-025,,05SP025,,N05SP025,,BKNTB01#025@#*****,BKN05SP025@#*****

Inrush-limiting NTC, Model(s): NTB02-004,,05SP004,,N05SP004,,BKNTB02#004@#*****,BKN05SP004@#*****

Inrush-limiting NTC, Model(s): NTB02-005,,05SP005,,N05SP005,,BKNTB02#005@#*****,BKN05SP005@#*****

Inrush-limiting NTC, Model(s): NTB02-006,,05SP006,,N05SP006,,BKNTB02#006@#*****,BKN05SP006@#*****

Inrush-limiting NTC, Model(s): NTB02-007,,05SP007,,N05SP007,,BKNTB02#007@#*****,BKN05SP007@#*****

Inrush-limiting NTC, Model(s): NTB02-008,,05SP008,,N05SP008,,BKNTB02#008@#*****,BKN05SP008@#*****

Inrush-limiting NTC, Model(s): NTB02-009,,05SP009,,N05SP009,,BKNTB02#009@#*****,BKN05SP009@#*****

Inrush-limiting NTC, Model(s): NTB02-010,,05SP010,,N05SP010,,BKNTB02#010@#*****,BKN05SP010@#*****

Inrush-limiting NTC, Model(s): NTB02-012,,05SP012,,N05SP012,,BKNTB02#012@#*****,BKN05SP012@#*****

Inrush-limiting NTC, Model(s): NTBR25-045,,05SP045,,N05SP045,,BKNTBR25#045@#*****,BKN05SP045@#*****

Inrush-limiting NTC, Model(s): NTBR3-030,,05SP030,,N05SP030,,BKNTBR3#030@#*****,BKN05SP030@#*****

NTC sensor, Model(s): TDC03A110,,BKTDC03A110@#*****, TDC03C225,,BKTDC03C225@#*****, TDC03C233,,
BKTDC03C233@#*****

PTC current limiter, Model(s): BK16-1000-S@,,BK16-1100-S@,,BK16-1200-S@,,BK16-1400-S@,,BK16-300-S@,,BK16-400-S@,,
BK16-500-S@,,BK16-600-S@,,BK16-700-S@,,BK16-800-S@,,BK16-900-S@,,BK250-030-D@,,BK250-040-D@,,BK250-060-D@,,
BK250-080-D@,,BK250-090-D@,,BK250-110-S@,,BK250-120-S@,,BK250-145-S@,,BK250-180-D@,,BK250-180-S@,,BK250-200-,
D@,,BK250-200-S@,,BK250-400-S@,,BK250-600-S@,,BK250-800-S@,,BK30-090-S@,,BK30-110-S@,,BK30-135-S@,,BK30-160-S@,,
BK30-185-S@,,BK30-200-S@,,BK30-250-S@,,BK30-300-S@,,BK30-400-S@,,BK30-500-S@,,BK30-600-S@,,BK30-700-S@,,BK30-,
800-S@,,BK30-900-S@,,BK60-005-D@,,BK60-010-D@,,BK600-110-S@,,BK600-150-S@,,BK600-160-S@,,BK60-017-D@,,BK60-020-,
D@,,BK60-025-D@,,BK60-030-D@,,BK60-040-D@,,BK60-050-D@,,BK60-065-D@,,BK60-075-D@,,BK60-090-D@,,BK60-110-D@,,
BK60-110-S@,,BK60-135-D@,,BK60-160-D@,,BK60-185-D@,,BK60-250-D@,,BK60-300-D@,,BK60-375-D@,,SMD0603#004TF,,
SMD0603#010TF,,SMD0603#020TF,,SMD0603#025TF,,SMD0603#035TF,,SMD0603#050TF,,SMD0805#005TF,,SMD0805#010TF/24,,
SMD0805#010TF@,,SMD0805#020TF@,,SMD0805#035TF@,,SMD0805#050TF@,,SMD0805#075TF@,,SMD0805#100TFT@,,
SMD0805#110TF@,,SMD1206#010TF@,,SMD1206#012TF/48,,SMD1206#012TF@,,SMD1206#016TF@,,SMD1206#020TF/24@,,
SMD1206#020TF/30,,SMD1206#025TF/24@,,SMD1206#025TF@,,SMD1206#035TF/16@,,SMD1206#035TF/30,,
SMD1206#050TF/15@,,SMD1206#050TF/24,,SMD1206#050TF@,,SMD1206#075TF/13.2@,,SMD1206#075TF/16@,,
SMD1206#075TFT@,,SMD1206#110TF/16,,SMD1206#110TFT@,,SMD1206#150TFT@,,SMD1206#175TF@,,SMD1206#200TF@,,
SMD1210#005TF@,,SMD1210#010TF/60,,SMD1210#010TF@,,SMD1210#020TF@,,SMD1210#035TF/30,,SMD1210#035TF@,,
SMD1210#050TF/30,,SMD1210#050TF@,,SMD1210#075TF/24@,,SMD1210#075TF@,,SMD1210#110TF/12@,,
SMD1210#110TF/16@,,SMD1210#110TFT@,,SMD1210#150TF/12@,,SMD1210#150TF/16@,,SMD1210#150TFT@,,
SMD1210#175TF@,,SMD1210#200TF@,,SMD1812#010TF/60,,SMD1812#010TF@,,SMD1812#014TF@,,SMD1812#020TF@,,
SMD1812#020TF-J@,,SMD1812#030TF/60,,SMD1812#035TF/30@,,SMD1812#035TF/60,,SMD1812#050TF/30@,,
SMD1812#050TF/60,,SMD1812#050TF@,,SMD1812#075TF/24@,,SMD1812#075TF/33@,,SMD1812#075TF@,,
SMD1812#110TF/16@,,SMD1812#110TF/24@,,SMD1812#110TF/33@,,SMD1812#110TF@,,SMD1812#125TF/16@,,
SMD1812#125TF/6,4L@,,SMD1812#150TF/12@,,SMD1812#150TF/16@,,SMD1812#150TF/24@,,SMD1812#150TF/8@,,
SMD1812#160TF/16@,,SMD1812#160TF/8 (4L) @,,SMD1812#200TF/12@,,SMD1812#200TF/16@,,SMD1812#200TFT@,,
SMD1812#260TF/12@,,SMD1812#260TF/16@,,SMD1812#260TFT@,,SMD1812#300TFT@,,SMD2016#030TF@,,
SMD2016#050TF@,,SMD2016#075TF@,,SMD2016#100TF/33@,,SMD2016#100TF@,,SMD2016#150TF/33,,SMD2016#150TF@,,
SMD2016#200TF@,,SMD2016#260TF/24,,SMD2016#300TF,,SMD2016#500TF,,SMD2920#030TF@,,SMD2920#050TF@,,
SMD2920#075TF/60@,,SMD2920#075TF@,,SMD2920#100TF@,,SMD2920#110TF/60,,SMD2920#125TF@,,SMD2920#150TF@,,
SMD2920#185TF@,,SMD2920#200TF/24@,,SMD2920#250TF@,,SMD2920#260TF/24@,,SMD2920#260TF@,,
SMD2920#300TF/15@,,SMD2920#330TF,,SMD2920#400TF@,,SMD2920#500TF/16@,,SMD2920#500TF@,,SMD2920#600TF/12,

PTC current limiter, Model(s): SMD+1812B190TF%%% "+" - Can be any 1 alphanumeric character or blank. "%%%" – Can be any 3 alphanumeric characters.

PTC current limiter, Model(s): SMD+1812B200TF%%% "+" - Can be any 1 alphanumeric character or blank. "%%%" – Can be any 3 alphanumeric characters.

PTC current limiter, Model(s): SMD+1812B260TF%%% "+" - Can be any 1 alphanumeric character or blank. "%%%" – Can be any 3 alphanumeric characters.

PTC current limiter, Model(s): SMD+1812B270TF%%% "+" - Can be any 1 alphanumeric character or blank. "%%%" – Can be any 3 alphanumeric characters.

PTC current limiter, Model(s): SMD+1812B300TF%%% "+" - Can be any 1 alphanumeric character or blank. "%%%" – Can be any 3 alphanumeric characters.

PTC current limiter, Model(s): SMD+1812B350TF%%% "+" - Can be any 1 alphanumeric character or blank. "%%%" – Can be any 3 alphanumeric characters.

PTC current limiter, Model(s): SMD+1812B370TF%%% "+" - Can be any 1 alphanumeric character or blank. "%%%" – Can be any 3 alphanumeric characters.

PTC current limiter, Model(s): SMD+2920B300TF%%% "+" - Can be any 1 alphanumeric character or blank. "%%%" – Can be any 3 alphanumeric characters.

PTC current limiter, Model(s): SMD+2920B330TF%%% "+" - Can be any 1 alphanumeric character or blank. "%%%" – Can be any 3 alphanumeric characters.

PTC current limiter, Model(s): SMD+2920B500TF%%% "+" - Can be any 1 alphanumeric character or blank. "%%%" – Can be any 3 alphanumeric characters.

PTC current limiter, Model(s): SMD+2920B600TF%%% "+" - Can be any 1 alphanumeric character or blank. "%%%" – Can be any 3 alphanumeric characters.

PTC current limiter, Model(s): SMD+2920B700TF%%% "+" - Can be any 1 alphanumeric character or blank. "%%%" – Can be any 3 alphanumeric characters.

- Unique Conditions of Acceptability are indicated in the individual Recognition Report available from the manufacturer.

Last Updated on 2024-12-06

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL Solutions' Follow - Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL Solutions' Follow - Up Service. Always look for the Mark on the product.

UL Solutions permits the reproduction of the material contained in Product iQ subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from Product iQ with permission from UL Solutions" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "©2025 UL LLC."